

SDMO 3-Phase Generators: Canopies

Discover our modular canopy concept and transparently appreciate its advantages ! In addition to noise reduction, this particularly economical concept enables you to optimise your generator set's footprint and to benefit from features such as easy handling and a retention bund...



CANOPY 127



CANOPY 126



CANOPY 127



CANOPY 128



CANOPY 129



CANOPY 226



CANOPY 228



CANOPY 229



CANOPY 129

SDMO 3-Phase Generators: Canopies

Discover our modular canopy concept and transparently appreciate its advantages !
In addition to noise reduction, this particularly economical concept enables you to optimise your generator set's footprint and to benefit from features such as easy handling and a retention bund...

	TYPE	CANOPY	TANK	DIMENSIONS L x W x H (m)	WEIGHT (Kg)	LWA	ACOUSTIC POWER - 50HZ dB(A)@1m dB(A)@7m	
MONTANA	J33	127	100	2.06 x 0.9 x 1.42	970	95	78,4	68
	J44K	127	100	2.06 x 0.9 x 1.42	1040	91.1	79,5	65
	J66K	28	180	2.30 x 1.08 x 1.68	1490	96,4	79,5	70
	J77K	128	180	2.30 x 1.08 x 1.68	1530	96,4	79,5	70
	J88K	128	180	2.30 x 1.08 x 1.68	1530	96,4	79,5	70
	J110K	129	190	2.55 x 1.17 x 1.68	1820	94,5	77	67
	J130K	226	340	3.51 x 1.20 x 1.83	2020	96,1	78,1	68
	J165K	226	340	3.51 x 1.20 x 1.83	2110	96,1	78,6	68,8
	J200K	226	340	3.51 x 1.20 x 1.83	2200	96,6	78,6	68,8
	J220K	226	340	3.51 x 1.20 x 1.83	2364	96,6	78,6	68,8
	J300K	227	390	4.00 x 1.38 x 2.13	3215	98,2	79,5	69,5
	J400K	228	470	4.48 x 1.41 x 2.43	4170	95,5	76,2	66,5
	J440K	228	470	4.48 x 1.41 x 2.43	4170	95,6	76,3	66,6
	ATLANTIC	V220K	227	390	4.00 x 1.38 x 2.13	3050	94,5	75,7
V275K		227	390	4.00 x 1.38 x 2.13	3200	97,8	79	69
V330K		228	470	4.48 x 1.41 x 2.43	3980	98,6	79,4	70
V375K		228	470	4.48 x 1.41 x 2.43	3910	98,6	79,4	70
V410K		228	470	4.48 x 1.41 x 2.43	4320	98,8	79,5	69,5
V440K		228	470	4.48 x 1.41 x 2.43	4320	98,8	79,2	69,2
V500K		229	500	5.03 x 1.56 x 2.43	4660	99,3	79,7	69,7
V550K		229	500	5.03 x 1.56 x 2.43	4725	99,3	79,7	69,7
V630K		230	610	5.03 x 1.69 x 2.66	5300	99,5	81,8	71,5



SDMO makes its generating sets comply with the directive 2000/14/CE and the validation of its products is controlled by an approved laboratory, the CETIM.